



Hach 934-AH Filters, 110mm, 100/pk

Продукт №: 2511211
BGN Цена: Свържете се с нас
Не е показана дата на доставка

Hach 934-AH Filters are specified for use in Standard methods 2540 C, 2540 D and 2540 E. Fast flow rate, fine porosity and 1.5 μm particle retention have made this binderless borosilicate glass microfiber filter the accepted industry standard for over 50 years. Hach 934-AH Filters can withstand temperatures over 500°C, which is a unique and especially important feature for laboratories performing Fixed and Volatile Suspended Solids analysis of water and wastewater.

The trademark 934-AH is owned by GE Healthcare/Whatman Inc. and used under exclusive license for purposes of private label.

Спецификации

Диаметър:	110 mm
Единица:	100/pk
Материал:	Glass Microfiber
Обем / опаковка, размер:	100 /pk
Пори, размер:	1.5 μm