



Pocket Pro TDS тестер с голям обхват

Продукт №:

9531300

BGN Цена:

Свържете се с нас

Налично

Take The Guesswork Out of Your Measurements.

Hach Pocket Pro and Pro+ deliver accurate results with built in diagnostics, replaceable batteries, and a large, easy-to-read LCD screen.

Сигурни резултати

Easy calibration steps take the guesswork out of calibrating the sensor to keep it in optimum condition.

Спестява време и пари

Easy to replace AAA batteries and convenient sample cup make maintenance and measurements simple

Лесна употреба

The large LCD screen is easy to read; backlighting is included on Pocket Pro⁺ models, allowing measurement in almost any lighting environment.

Спецификации

Ассигура:	2% от пълната скала
IP клас на корпуса:	IP67
Range:	0 - 10,00 ppt
TDS factor:	Регулируем; 0.71 по подразбиране
Гаранция:	24 месеца
Изисквания за батерии:	4, AAA
Какво има в кутията:	Includes: tester, 4 AAA batteries, lanyard and quick start guide.
Обем на проба:	7 mL
Параметър:	TDS, Темп.
Работен температурен диапазон:	0 - 50 °C
Резолуция:	0,01 ppt
Ръчно, езици:	Английски, френски, немски, италиански, испански
Фоново осветление:	Не

Какво има в кутията

Includes: tester, 4 AAA batteries, lanyard and quick start guide.