



FP 360 sc Oil-in-water probe, 0.1-15 ppm Oil, ss, 10m, with cleaning

Продукт №:

LXV441.99.11201

BGN Цена:

Свържете се с нас

Не е показана дата на доставка

Continuous oil-in-water monitoring for the right price

Fluorescence probe for PAH/Oil in water measurements. Stainless steel enclosure, 10 m cable, with cleaning unit.

Even the smallest oil traces impair water quality. The probe monitors surface waters, process water and industrial water continuously for even traces of mineral oil contamination. The highly sensitive UV fluorometer is immersed directly in the medium.

For reliable, long term stable hydrocarbon monitoring, intensity fluctuations

of the flashlamp are compensated. Influences associated with daylight are automatically eliminated.

The probe can be combined with additional sensors on the SC controllers.

The right technology for the right price

Due to its unique combination of submersible probe design and UV fluorescence sensing technology, the FP360 sc delivers the best technology to detect oil in water and is priced below competitive UV fluorescent instruments.

Minimal maintenance

The FP360 sc has no tubes, pumps, or valves that can foul or require constant maintenance interventions. Maintenance is limited to occasional wiping of the sensor's measurement window and a calibration once every two years.

Reduced laboratory testing

While laboratory testing is the ultimate method of measuring oil in water, it is a long and complex process that requires special equipment and trained lab personnel. The FP360 sc provides a cost-effective, continuous online monitoring solution to maintain process control and avoid oil contamination with minimal laboratory testing.

High sensitivity and selectivity

The FP360 sc can detect and measure polycyclic aromatic hydrocarbons (PAHs) from 1.2 ppb to up to 5000 ppb ($\mu\text{g/L}$). This is approximately equivalent to a concentration of mineral oil between 0.1 to 150 ppm (mg/L). Furthermore, the FP 360 sc method of detection makes it impervious to interferences by turbid water or natural organic and biological matter that impact online light scattering, UV absorbance, and VIS fluorescence instruments.

One to eight sensors

The Hach Digital Controller Family can receive data from up to eight Hach digital sensors, including oil-in-water, suspended solids, turbidity, pH/ORP, dissolved oxygen, conductivity, ammonium, phosphate, SAC, and nitrate in any combination.

There's no complicated wiring or set up procedures with the family of controllers. Just plug the sensor to any Hach digital controller and it's ready to use because it's "plug and play."

Спецификации

Body Material:	Stainless Steel
pH стойност (и):	≥ 4
Време за отговор T90:	10 s
Възбуждане:	Wavelength 254 nm
Възпроизводимост:	2.5 % of measured value at constant temperature
Гаранция:	24 месеца
Детектор:	UV photodiode with interference filter; Compensation of daylight and flashlamp intensity fluctuations
Диаметър:	68 mm
Диапазон на налягането:	Max. 30 bar (measurement probe)
Дължина:	311 mm
Дължина на кабела:	10 m (32.8 ft)
Измерване метод:	UV fluorescence method for polycyclic aromatic hydrocarbons (PAH)
Измерване, диапазон:	0 - 500 ppb (µg/L) (PAH) or 0.1 - 15 ppm (mg/L) (Oil)
Какво има в кутията:	Oil-in-water probe, user manual
Калибриране:	Factory calibrated with UV fluorescence standard or process calibration with results of a grab sample analysis.
Материал:	Housing: Stainless steel 316Ti (1.4571)
Материал на тялото (измервателния уред):	Stainless Steel
Околна температура:	-5 - 45 °C
Почистване на сензора:	Yes
Светлинен източник:	Miniature xenon flashlamp with interference filter
Тегло:	2.8 kg
Температура на проба:	1 - 40 °C
Условия на съхранение:	-40 °C - 60 °C

Какво има в кутията

Oil-in-water probe, user manual

Задължителни аксесоари

- Модул с дисплей SC1000 (Item LXV402.99.00001)
- Контролер SC4500, Prognosys, 5 изхода за mA, 2 цифрови сензора, 100 - 240 VAC, без захранващ кабел (Item LXV525.99A11551)
- Контролер SC4500, може да работи с Claros, 5 изхода за mA, 2 цифрови сензора, 100 - 240 VAC, без захранващ кабел (Item LXV525.99AA1551)
- Контролер SC4500, може да работи с Claros, 5 изхода за mA, 2 цифрови сензора, 100 - 240 VAC, щепсел по стандарт на ЕС (Item LXV525.99CA1551)
- Контролер SC4500, Prognosys, 5 x mA изход, 1 цифров сензор, 100 - 240 VAC, без захранващ кабел (Item LXV525.99A11501)
- Контролер SC4500, Prognosys, 5 x mA изход, 2 цифрови сензора, 24 VDC, без щепсел (Item LXV525.99Z11551)