



Be Right™



CPVC Immersion Mount Assembly

Продукт №: МН432G
BGN Цена: Свържете се с нас
Повикване за дата на доставка

Mounting hardware for immersion mount of analogue and digital convertible inductive conductivity sensors.

Each immersion hardware includes a 1/2-inch diameter x 4 foot long pipe, 1/2 x 3/4-inch NPT coupling, and plastic pipe-mount junction box with terminal strip. Used for 3700-series and PC/RC series sensors.

Спецификации

Диаметър:	12.7 mm
Дължина:	1219 mm
Материал:	CPVC
Специални бележки:	Composition: Pipe, 1/2" / 3/4" NPT adapter coupling, plastic pipe-mount junction box with terminal strip