



Blender, Two Speed, 1.2 L, 240 Vac-50/60 Hz

Продукт №:

2616102

ОСТАРЯЛ АРТИКУЛ

Този артикул вече не е наличен.

This blender is tough enough to handle homogenizing wastewater, sludge, soil or heavy weight food samples for superior analytical results. Both models have thick walled glass containment jars and durable, rust free stainless steel blades. Two-piece vinyl and styrene lid.

Спецификации

Електротехнически спецификации:	240 Vac, 50/60 Hz
Инструмент:	All except DR/4000, PC II
Метод, номер:	8006
Обем / опаковка, размер:	1 each