



Be Right™



## Installation armature, inline fitting, stainless steel, for Solitax inline sc and Solitax highline sc

Продукт №:

LZX461

BGN Цена:

Свържете се с нас

Налично

Assembly fitting for sensor for evacuated and depressurized pipeline.

---

### Спецификации

Дължина:	210 mm installed
Материал:	High Grade Steel
Специални бележки:	Dimension - Pipe installation fitting for insertion sensors
	DN 65 / PN 16 DIN 2633;
Тегло:	3,7 kg