



## Acidification/Cleaning Unit for Amperometric Sensors

Продукт №: LZY051  
BGN Цена: Свържете се с нас  
Доставка до 2 седмици

Many amperometric processes have optimal pH ranges in which they will be most accurate and produce the best results. Adding an acidification/cleaning unit onto instruments such as the CL10 sc can help to ensure that samples stay range that is favorable for measurement.

---

### Спецификации

Depth panel:	107 mm
Height (panel):	270 mm
Width:	250 mm
Гаранция:	24 месеца
Дължина на кабела:	1 m digital
Изисквания към захранването (напрежение):	12 V DC
Какво има в кутията:	Acidification Unit, Carboy, 1 M digital extension cable, Tubing Kit, and Instructions.
Материал:	Carboy: PEHD (high-density polyethylene)
Обем:	10 L chemicals not supplied
Поток:	Min 0.24, max. 1 mL/min
Предпазител, клас:	T, 250 mA, 250V
Процесна връзка:	0.125 " NPT (for tube fittings)

---

### Какво има в кутията

Acidification Unit, Carboy, 1 M digital extension cable, Tubing Kit, and Instructions.