



**Be Right™**



## **Flow cell for 1" NPT sensor**

<b>Продукт №:</b>	<b>7300800</b>
BGN Цена:	Свържете се с нас
Повикване за дата на доставка	

The flow cell can be used for either the pH/D and NH<sub>4</sub>D (ammonium ISE) or NO<sub>3</sub>D (nitrate ISE) sensors. The flow cell has many features and benefits. A clear body enables quick inspection of the sensor and accumulated debris. Complete Sensor Immersion ensures good temperature compensation. Quick disconnects enable easy removal of the sensor for service. Large Porting, 3/8 inch inlet and 1/2 inch outlet, minimizes flow cell plugging due to debris. Tangential Inlet Porting introduces a vortex in the flow stream. This vortex separates heavy particles and ensures good mixing of process fluid inside the flow cell.