



Be Right™



## Orbisphere 6110 Total O<sub>2</sub>/CO<sub>2</sub> Package Analyser & Installation Kit

Продукт №:

DG6110-SYS

Опасен

EUR Цена:

Свържете се с нас

Доставка до 2 седмици



### Total Package Analyser for Oxygen & Carbon Dioxide measurements

The Orbisphere 6110 boasts the latest technology in final package analysis for measurements of Total Package Oxygen, Headspace Oxygen and Dissolved Oxygen; as well as dissolved Carbon Dioxide and Headspace Volume. It has been designed to meet the practical needs of both lab and at-line environments. The high-quality touch-screen facilitates measurement customisation on all types and sizes of cans or bottles, as well as providing critical information on the health of the instrument. Utilisation of this instrument has been proven to provide critical quality information of the final package, increasing process control and beverage quality.

#### Fast, effective operation

The 6110 delivers repeatable analysis with minimal operator intervention. The package positioning aid with laser crosshairs confirms optimal placement and the intuitive touch-screen interface ensures product sampling is completed quickly, easily, and consistently for both line operators and lab personnel. There is no sample preparation necessary for total package and head space oxygen analysis.

#### Reliable and flexible

The 6110 Total Package Analyser operates on all types of cans and bottles due to its unique gas extraction and piercing system, resulting in reliable analysis with no container leakages. The CO<sub>2</sub> analysis measurement provides accurate results at any temperature, without having to warm the sample. The 6110 can also compensate CO<sub>2</sub> results for any package Nitrogen content – a perfect choice for analysis directly at the filler.

#### Gas phase measurement

The Hach Orbisphere 6110 analyses beverages without removing any product from its container. The measurement takes place in the gas phase, so there is no direct liquid contact with the 6110's sensing technology or sampling path. This reduces maintenance by eliminating hassles such as bleaching tubing and replacing valves to prevent fouling.

#### Maximise the uptime of your 6110 Total Package Analyser

Our expert service team works in partnership with you to provide professional start-up and commissioning and regular maintenance for your 6110 Total Package Analyser to ensure it is in the optimal condition. Please speak with your local Hach representative for service offerings in your region..

---

## Спецификации

Installation requirement:

Power requirements: 100/240 VAC, 50/60 Hz

Purge gas: CO<sub>2</sub> with purity >99.9% at 6 to 7 bar abs (87 to 102 psi)

Laser Class:

A Class 1 LASER is installed in this instrument.

Exposure to the beam of a Class 1 LASER will not result in eye injury.

Intrabeam viewing of Class 1 laser products which emit visible radiant energy may still produce dazzling visual effects, particularly in low ambient light.

Operating system:	Windows CE 4.2
Package settings:	Closure types: metallic, PET
	Package height:
	min. 90 mm (3.54 in.)
	max. 340 mm (13.39 in.)
	Package volume: min. 150 mL
Typical analysis time:	Approximately 4 minutes
Възможности за комуникация:	1x Ethernet, 1x USB-A
Гаранция:	24 месеца
Дисплей, тип:	Digital TFT VGA (640 x 480) colour touch screen
Единица:	O <sub>2</sub> Concentration: ppb, ppm
	CO <sub>2</sub> Concentration: v/v, g/kg, g/L %W
	Total Package Quantities: mg, mL, mg/L, mL/L, µg/L
	Pressure: bar, mbar, psi
	Temperature: °F, °C, K
Изисквания към захранването (Hz):	50/60 Hz
Изисквания към захранването (напрежение):	100/240 V AC
Измерване, диапазон:	O <sub>2</sub> : 1 ppb - 12 ppm
	CO <sub>2</sub> : 0,75 - 5 v/v or 1,5 - 10 g/kg
Какво има в кутията:	Orbisphere 6110 Total Package Analyser (sensors pre-installed) with installation kit and user manual. See user manual on downloads tab for installation kit components.
Ограждение, клас:	IP20
Повторяемост:	TPO: ±5 µg/L / ±10%, whichever is greater
	CO <sub>2</sub> : ±0.05 v/v or 0.10 g/kg ±2 %, whichever is greater, measured on equilibrated packages at 10 - 25 °C
Размери (В x Ш x Д):	942 mm x 540 mm x 537 mm
Сертификати за съответствие:	European directives: Low voltage 2006/95/EC; EMC 2004/108/EC
	Electromagnetic compatibility standards: EN61326
	Safety standard: IEC/UL/CSA 61010-1
	Safety of Laser products: IEC/UL/CSA 60825-1
Тегло:	55 kg
Условия на работа:	Package temperature: -2 - 30 °C (28 - 86 °F) Package pressure: 1.4 - 6.8 bar (20 - 73 psi) Ambient temperature: 0 - 40 °C (32 - 104 °F)

---

## Какво има в кутията

Orbisphere 6110 Total Package Analyser (sensors pre-installed) with installation kit and user manual. See user manual on downloads tab for installation kit components.