



pH glass electrode, refillable, pure water applications

Продукт №:

LZY025

EUR Цена:

Свържете се с нас

Налично

pH electrode for use in ultra-pure water

Specially developed for use in ultra-pure water

Refillable glass electrodes for special requirements and high-precision measurements

Improved durability through triple ceramic diaphragm

Easy to install in stainless steel or polypropylene flow fittings

Спецификации

Reference system:	Ag/AgCl
Време за отговор T98%:	< 30 s
Гаранция:	6 месеца
Диафрагма:	Triple ceramic
Дължина:	120 mm
Електрод, материал на стеблото:	Glass
Електролит:	KCl liquid
Измерване, диапазон:	0 - 12 pH
Кабелна връзка:	Plug head S7
Работен температурен диапазон:	-30 - 80 °C
Тегло:	0,15 kg
Температурен датчик:	None