



## Hach 934-AH Filters, 125mm, 100/pk

Продукт №: 2511212  
BGN Цена: Свържете се с нас  
Не е показана дата на доставка

Hach 934-AH Filters are specified for use in Standard methods 2540 C, 2540 D and 2540 E. Fast flow rate, fine porosity and 1.5  $\mu\text{m}$  particle retention have made this binderless borosilicate glass microfiber filter the accepted industry standard for over 50 years. Hach 934-AH Filters can withstand temperatures over 500°C, which is a unique and especially important feature for laboratories performing Fixed and Volatile Suspended Solids analysis of water and wastewater.

934-AH is a registered trademark of Whatman, Inc./GE Healthcare and used under license.

---

### Спецификации

Диаметър:	125 mm
Единица:	100/pk
Материал:	Glass Microfiber
Обем / опаковка, размер:	100 /pk
Пори, размер:	1.5 $\mu\text{m}$