



Be Right™



AnaShell Analytical Cabinet Type AS1050, H=2.14m x W=0.9m x D=0.5m, for one analyser plus sample preconditioning

Продукт №:

AS1050

BGN Цена:

Свържете се с нас

Weather- and corrosion-resistant analyser cabinet as turnkey complete solution

The compact AnaShell analyser cabinets protect your measurement technology reliably and sustainably - even when space is limited. One analyser, plus the associated sample preconditioning unit, is kept safe from harmful vapours, vibrations, precipitation, solar radiation and temperature fluctuations.

Safe housing with laboratory-like conditions

The insulated AnaShell analyser cabinets, including the base plate, are made of glassfiber reinforced polyester (GRP) on a stainless steel frame. The self-supporting construction has a high mechanical strength and withstands even extreme weather conditions. Protection class IP54 (NEMA 3X) means dust-tight and water jet proof, ensuring your analysers are well protected. In conjunction with an air conditioning system, consistent ambient conditions can be achieved - ideal conditions for accurate results.

Professional Integration

We develop your AnaShell enclosure as a turnkey complete solution. Sample perconditioning and analysers are permanently mounted on chemical resistant High Pressure Laminate (HPL) plates with galvanized modular mounting profiles (MMP). The necessary connections are planned accordingly, all cables and hoses are clearly marked and easy to read. You will receive extensive documentation for your cabinet, e.g. technical drawings for electrics, 2D floor plan and P&ID.

Safety is a top priority

AnaShell cabinets intended for outdoor installation come with lightning protection. They feature two separate grounding systems: equipment (AC safety) and isolated shield grounding system. All non-energized parts of the equipment are bonded to the shelter equipment (AC safety) ground bus through dedicated bonding cables. High quality door hinges are designed for the long service life of the cabinet.

Small installation effort, fast commissioning

Each AnaShell enclosure is mounted incl. all analysers in our plant and tested before shipping. Four lifting and mounting brackets (90° rotatable) facilitate transport and installation on site. Unload, unpack, set up, connect - ready for the first sample.

Certification included

AnaShell enclosures have passed the necessary tests and are certified with CE Declaration of Conformity according to Machine Directive 2006/42/EC of the European Parliament and of the Council of 17 May 2006 on machinery and EMC Directive 2014/30/EU of the European Parliament and of the Council of 26 February 2014 on the harmonization of the laws of the Member States relating to electromagnetic compatibility.

Спецификации

Heating system:

Optional, combinable:

- Thermostatically controlled electrical heating (1200 W)
- Thermostatically controlled air conditioning unit (cooling only, 1500 W)

Signal junction box:

Optional:

- One (1) combined local signal junction box for analog signals (4 - 20 mA, max. load 500 Ohm) and alarms (potential free contacts, max. 24 V DC). Max. 12 pairs (equals 24 terminals). Mounted on the outside wall of the cabinet (shielded by pair).
- Two (2) local signal junction boxes. One box for analog signals (4 - 20 mA, max. load 500 Ohm). One box for alarms (potential free contacts, max. 24 V DC). Max. 6 pairs (equals 12 terminals) per junction box. Mounted on the outside wall of the cabinet (shielded by pair).
- Ethernet switch for serial communication, installed in the local power distribution panel. Plus one (1) local signal junction box, mounted on the outside wall of the cabinet.
- Ethernet switch for serial communication, installed in the local power distribution panel. Plus two (2) local signal junction boxes, mounted on the outside wall of the cabinet.

Вентилация:

Optional:

- Natural ventilation: by means of two ventilation openings installed near diagonal corners on opposite walls at floor and top level.
- Forced ventilation: from outside to inside with a single electrical motor driven fan, which is sized to supply a minimum volume equivalent to six air changes per hour. Both the fan (ventilation inlet) and the ventilation outlet are installed near diagonal corners on opposite walls at floor and top level.
- Purge ventilation: applicable for corrosive environments. Instead of outside air a purge of instrument air (IA) is used. The purge is distributed by a collector with individual adjustable silencers. Purge inlet is at the top, and outlet ventilation is at the bottom and top, protected by check valves. With this option there is always a slight overpressure inside the cabinet.

Захранване:

Each analyser is powered by a black colored service switch with lock position (suitable for LOTO Lock Out Tag Out) and has an individual circuit breaker in the local power distribution panel. An electrical power socket is not needed.

According to CE regulations a local main electrical power switch is mandatory. Options (always with lock position, suitable for LOTO Lock Out Tag Out):

- One (1) local main electrical power switch, single phase 230 VAC / 50 Hz - UPS or non-UPS
- Two (2) local main electrical power switches, single phase 230 VAC / 50 Hz - UPS and non-UPS
- One (1) local main electrical power switch, triple phase 3x380 VAC+N / 50 Hz - UPS or non-UPS
- Two (2) local main electrical power switches, triple phase 3x 380 VAC+N / 50 Hz - UPS and non-UPS
- One (1) local main electrical power switch, single phase 230 VAC / 50 Hz - UPS or non-UPS, plus one (1) local main electrical power switch, triple phase 3x380 VAC+N / 50 Hz - UPS or non-UPS

Какво има в кутията:

AnaShell analytical shelter type AS1050 in ordered configuration; process instrumentation and sample preconditioning pre-assembled and mounted ex works according to order

Клас на защита:

Depending on configuration

Материал:

Shelter material: Sandwich construction made of GRP (glass fiber reinforced polyester) by low pressure Resin Transfer Molding (RTM) using UV resistant gelcoat impregnation process.

Base frame material: SS316L (1.4404), including four SS316L (1.4404) lifting and transport brackets, twistable by 90° mounted to the base frame.

Insulation: 2 cm (0.79") thickness, K = 1.2 W/m²K

AS1050

Модел:

Complementary equipment:

Опции:

- Additional electrical sockets 230 VAC / 6A (max. 2)

- Protective rain and sun roof

(H x W x D) 2.14 m x 0.9 m x 0.5 m

Размери:

Сертификати:

CE Declaration of Conformity conform Machine Directive 2006/42/EC und EMC Directive 2014/30/EU

Тегло:

200 kg

Какво има в кутията

AnaShell analytical shelter type AS1050 in ordered configuration; process instrumentation and sample preconditioning pre-assembled and mounted ex works according to order